

## 315C

### Pocket Digital Thermometer

**To measure temperature with the 315C follow these simple instructions:**

Select either the Fahrenheit or Celsius mode:

- With the unit "OFF" press and continue to hold the ON/OFF button. The LCD will alternate between F and C.
- Release the ON/OFF button when desired measurement mode appears on the LCD.

Remove the protective sheath from the stem.

Press the ON/OFF button.

Insert stem into area or object to be tested. At least 1/2 inch of the stem must be inserted.

**WARNING:** The stem is a sharp and pointed object which can be dangerous.

The Data Hold Function is used by pressing the D-H button when taking a measurement. The measurement will flash on the LCD when Data Hold is activated. To return to normal operation, press and release the D-H button a second time.

Press the ON/OFF button to end operation or the unit will automatically power off after approx. 35 minutes.

**Specifications:**

Temperature Range	-58 to 300 F/-50 to 150 C
Resolution	0.1 Degrees
Accuracy	+/- 2 F, +/- 1C
Sampling Time	1.5 Seconds
Battery	(LR44) A044



Test Products International  
9615 SW Allen Blvd. #104,  
Beaverton, OR 97005-4814 USA

Ph: 503-520-9197      Fax: 503-520-1225