

Pocket Digital Thermometer

To measure temperature follow these simple instructions:

Selecting Fahrenheit or Celsius mode:

- With the unit “OFF” press and continue to hold the ON/OFF button. The LCD will alternate between °F and °C
- Release the ON/OFF button when desired measurement mode appears on the LCD

Remove the protective sheath from the stem

Press the ON/OFF button.

Insert stem into area or object to be tested. At least ½ inch of the stem must be inserted.

Warning: The stem is a sharp and pointed object which can be dangerous.

The Data Hold Function is used by pressing the D-H button when taking a measurement. The measurement will flash on the LCD when Data Hold is activated. To return to normal operation, press and release the D-H Button a second time.

Press the ON/OFF button end operation or the unit will automatically power off after approx. 35 minutes.

Specifications:

Temperature Range	-58 to 300 °F/-50 to 150 °C
Resolution	0.1 Degrees
Accuracy	+/- 2 °F, +/- 1 °C
Sampling Time	1.5 Seconds
Battery	(SR44) A044



Test Products International
9615 SW Allen Blvd. #104,
Beaverton, OR 97005-4814 USA

Ph: 503-520-9197 Fax: 503-520-1225