

368 Pocket Digital Thermometer

To measure temperature with this unit follow these simple instructions:

Press the ON/SET button to power on and **enter scan mode** and take measurements. Unit will automatically shut off after 30 seconds.

Changing °C/°F: Press and release the ON/SET button then press the MODE button repeatedly to make the °C or °F annunciator flash on the LCD. Press the ON/SET button to select °C or °F.

OTM (One Time Measurement): Press and release the ON/SET button and press MODE repeatedly until the OTM annunciator is seen on the LCD. Press and release the ON/SET button to display temperature on the LCD. Readings are held on display for 10 seconds. Ideal for hard to reach locations.

Low Battery Indicator: Will be displayed when battery level becomes less than 2.65 Volts.


HI or LO: Will be displayed when the measured temperature is outside of the measurement range specification.

Specifications:

Range	-7° to 248°F or -22° to 120°C
Operating Temp	32° to 104°F or 0° to 40°C
Accuracy	2% or reading or $\pm 2^{\circ}\text{C}$, whichever is greater
Response Time	Less than 0.5 second
Resolution	0.1 °F/C
Emmissivity	0.95 fixed
Distance to Spot Ratio	1:1.3
Battery	A003
Battery Life	50 hours continuous use, auto off after 30 sec.

THIS INSTRUMENT is in compliance with EN 50 081-1: 1992, EN 50 082-1:1992, IEC 801-2:1984, IEC 801-3:1984, IEC 801-4:1988

Test Products International, Inc.
Beaverton, OR 97005
503-520-9197 Fax: 503-520-1225
email: info@tpi-thevalueleader.com

 WARNING	
<ul style="list-style-type: none">• INGESTION HAZARD: This product contains a button cell or coin battery.• DEATH or serious injury can occur if Ingested.• A swallowed button cell or coin battery can cause Internal Chemical Burns in a little as 2 hours.	